Product Data Sheet

CCT 1000-TL I (+55°C)

Relevant Test Standards:

Cyclic Corrosion Tests:

- DIN EN ISO 11997-1:2006 Cycle B (previously VDA 621-415)
- VW PV 1210 (climate module required)

Water Condensation Tests:

- DIN EN ISO 6270-2:2005
- BS 3900 F2
- BS 3900 F15
- ASTM D2247



Salt Spray Tests:

- DIN EN ISO 9227
- DIN 50942, DIN 53167
- ASTM B 117-73, ASTM B 287-74
- ASTM B 368-68
- ISO 7253 ISO 3678
- BS 1224, BS 2011, BS3900 F4
- BS 3900 F12
- BS 5466 Part I, BS 5466 Parts 2 + 3
- NFX 41002,
- AS 21331 Section 3.1
- SIS 1841190
- JIS Z 2371
- IEC 60028-2-11 KA

Legend

- **CH Constant Humidity**
- **AT Alternating Temperature**
- **AHT- Alternating Humidity and** Temperature
- AIR Forced air circulation
- AWRF Automatic water refill

Order Information

Basic model: CCT 1000-TL I Article numbers: V.735.065.150

Sales & Support: **5205 87963 0** Monday to Friday

8:00 am - 17:00 pm

VLM GmbH Heideblümchenweg 50 33689 Bielefeld

info@vlm-labtec.com www.vlm-labtec.com

Specification subject to changes Pictures might differ from original



Customer Benefits

- Operating temperature from ambient up to +55°C
- Time and energy savings over the operational lifetime the bottom of the test chamber is made of steel which allows fast and uniform heat transfer making this test chamber perfectly suitable for accelerated corrosion tests
- The steel bottom of the test chamber makes the test chamber more robust and less susceptible for damages compared to the competitive products made of glass reinforced plastic
- Lower total cost of ownership compared to the competitive products where the test chamber is completely made of glass reinforced plastic (shorter test periods, better energy efficiency, easier for service and maintenance, longer life cycle, more resistive to mechanical damages)
- User friendly, intuitive and versatile controller (Jumo IMAGO) with color screen and password protection - most common corrosion tests are already preconfigured

1 CCT 1000-TL I | VLM GmbH



Product Description

Compact top loading corrosion test chest developed for conducting automated cyclic corrosion tests pursuant to the most common corporate (automotive) and international corrosion standards such as:

- DIN EN ISO 11997-1:2006 Cycle B (previously VDA 621-415)
- VW PV 1210 (external climate module required)

This cabinet can also conduct standard corrosion tests:

Product Data Sheet

CCT 1000-TL I (+55°C)

Relevant Test Standards:

Cyclic Climate Tests:

- DIN EN ISO 11997-1:2006 Cycle B (previously VDA 621-415)
- VW PV 1210 (climate module required)

Water condensation tests:

- DIN EN ISO 6270-2:2005
- BS 3900 F2
- BS 3900 F15
- ASTM D2247



Salt Spray Test:

- DIN EN ISO 9227
- DIN 50942, DIN 53167
- ASTM B 117-73, ASTM B 287-74
- ASTM B 368-68
- ISO 7253 ISO 3678
- BS 1224, BS 2011, BS3900 F4
- BS 3900 F12
- BS 5466 Part I, BS 5466 Parts 2 + 3
- NFX 41002,
- AS 21331 Section 3.1
- SIS 1841190
- JIS Z 2371
- IEC 60028-2-11 KA



Figure 1 Jumo Imago 500 controller

The following accessories are included:

- 6 rods for supporting test specimen
- 3 m exhaust hose Ø 75 mm
- 2 m drain water hose Ø 32 mm
- 1 female connector for compressed air hose (size no. 5)



| Technical Specifications | |
|---|---|
| Capacity | ca. 1000 L |
| Inner test chamber | ca. 1425 x 800 x 690 / 1005 mm |
| dimensions W/D/H1/H2 | |
| Outer dimensions of the | ca. 1895 x 890 x 1265 mm |
| casing (overall) W/D/H | |
| Required power supply | 230V, 50/60Hz, 2500W |
| Materials used | The walls of the chamber are made of Polypropylene while the bottom is made of stainless steel and coated with ECTFE. The walls have milled openings for supporting rods |
| Heating | Flat Micanite heaters under the bottom of the chamber for fast and uniform heat transfer |
| Sensors | 1x corrosion resistant and highly sensitive temperature sensor |
| Temperature stability | ±0,5°C |
| Aeration (type AIR) | timer controlled built-in fan (capacity ca. 16 m ³ /h) |
| Controller | Programmable Jumo IMAGO controller |
| | Note: Data logging is not possible |
| Weight | 250 kg |
| Communication | RS 232 interface (optional) |
| Other specification | |
| Purity demi water / fitting | < 5 µS/cm / ¾" outer diameter |
| Tap water (connection | Always via Ion-exchanging cartridge (¾" outer |
| type) | diameter) |
| Compressed Air | 6-8 bar (connection nipple size 5) |
| Waste water, drain | Pipe fittings (spiral hose 32mm) |
| Air exhaust pipe outer diameter | Pipe fitting (75 mm external diameter) |
| Number of supporting rods / max load | 6 stainless steel rods coated with plastic / 30 kg each |

Process Control

- User friendly, menu guided JUMO Imago controller with colour graphic display
- Restricted access for operators to three different operating levels
- Memory storage with the capacity to hold up to 50 test programs with most common corrosion tests already preconfigured in the factory
- The controller steers the external climate module for the tests which require air conditioning (typically PV 1210)
- Full overview of all digital and analog inputs / outputs

Operating System Water Condensation (CH) according to ISO 6270-2

- Flat heaters under the bottom of the chamber for uniform and rapid heating of the water in the trough
- Temperature stability in the chamber ± 0,5°C
- Automatic refilling of the test chamber (AWRF) for maintaining constant water level in the trough
- Parameters for standard water condensation tests are already preconfigured


Operating System Aeration

- Aeration with environmental air (aeration with warm air is optional) for forced air drying phase
- Adjustable air distribution system inside the test chamber for uniform drying of the test specimens
- Fan with controllable rotation speed
- Option: Air conditioning module for providing standard climate acc. to DIN 50014 (ISO 554): ambient air at 23°C ±2°C and 50% ±5% RH

2 CCT 1000-TL I | VLM GmbH Version: v9/09.03.2017

Product Data Sheet

CCT 1000-TL I (+55°C)



Operating System Salt Spray (according to ISO 9227)

- Electronically controlled diaphragm pump for accurate flow control of the test solution with automatic monitoring of the presence of the air in the pump system
- Adjustable high performance acrylic spray nozzle for an optimal generation and distribution of the salt fog
- Transparent humidifier made of heat resistant Borosilicate glass with a replaceable PE air filter
- Safety air pressure valve on the humidifier
- Over temperature protection of the humidifier
- Air purge function for rapid evacuation of the salt fog out of the chamber
- Accessories: 210 L PE storage reservoir for test solution (level indicator optional)

6

0

• **Option:** Nozzle for washing the test chamber after the salt spray test is finished




Figure 2 Mechanical dimension CCT 1000-TL-I